

verteiler	KB	AV	ST	AR	M0	D I	KT	SF	VS	US	KÜ
	WE	EL	LA	ZU	VK	UK	MC	SB	EK	SJ	SG

max. Bauteilhöhe 15 mm

d	*	*	*	Material/State Echelle	Produkt/Product/Produit Kunde/Customer/client	Werkstoff/Material/Matiere:
e	*	*	*		**	
b	*	*	*		**	
a	*	*	*			
0	Freigebe/Release Relaisement	*	*	Benennung/Title/Designation: BUSPLATINE 10 SLOT VME64X MONO Besteckbeispiele (BPU) Blz1 2 xxx 2	Freisatz-Tol Tolerance Tolér.:libre DIN 7168	
	Norm Revision	*	*	2.Nr./Drawing No. No. du document	Intern./Revisio Modification	Status
	Gepr./Approv	*	*	23001-540	000 53	12/12/92 I
	Gez./Drawn Des.	28.12.03	Schl.	***	Ersetzt für: replace/replace:	***
Ind SYM	Änder. Modification	Date Date	Norm Nom	3	2	1
	4					

Lieferant:

Schreff