



KEY FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUCT ATTRIBUTES

Product Type: Socket Strip

Socket Type: (6) C19

Socket Quantity: 6

Color: Black

Switched Outlets: No

Circuit Breaker: 1-pole, 16 A, Hy-Mag

Circuit Breaker Quantity: 2

Input Cable Length: 3 m

Input Cable Location: Front Feed

Input Current: 32 A

Input Voltage: 200-240 VAC, 1 PH

Interrupt Rating: 5 kAIC

Max Power Input: 7.44 kVA

Metering Type: None

Output Voltage: 200 – 240 VAC

Plug Type: IEC 60309 332P6 (IP44)

Rack Height: 1 U

Removable Input Cable: No

ADDITIONAL PRODUCT DETAILS

Modular, compact PDU. Ultra-Low Profile Design

Please order bracket for vertical mounting separately.

North America

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.