


31596-900 ADVANCEDTCA FRONT PANEL, REINFORCED WITH SPRING LOADING FOR IEA LEVER HANDLE, DIE-CAST END PIECE, 8 U, 6 HP, 1 MM, AL EXTRUSION



## KEY FEATURES

---

Configuration: Front panel with IEA handle (with/without spring loading)

Al extrusion; for mesh EMC sealing

## PRODUCT ATTRIBUTES

---

Product Type: Front Panel

Accessory Type: Front panel

Material: Aluminum

Front Finish: Raw

Rear Finish: Raw

Rack Height: 8 U

Height: 323.15 mm

Rack Width: 6 HP

Width: 29 mm

Depth: 1 mm

Package Quantity: 1

## ADDITIONAL PRODUCT DETAILS

---

AdvancedTCA front panel for spring-loaded IEA handle with die-cast end piece.

## CERTIFICATIONS

---



### North America

All locations

+1.763.422.2661

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
[nVent.com](https://nVent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.