



SCHROFF

MEN260HC-5.80ETM2 260HC HIGH CLAMP FORCE CARD-LOK



KEY FEATURES

Profile 6.35 mm (0.250") x 6.86 mm (0.270")

Weight 0.95 g/cm (0.085 oz/")

Length 96.5 mm (3.80") to 172.7 mm (6.80"), 12.7 mm (0.5") increments

Flexible mounting options

5 segment, shafted design

Average clamp force (4.80", black anodized) = 868 lbs

Screw actuated

Max expansion 8.26 mm (0.325")

Available with black anodized, hard black anodized, or electroless nickel plating

For cold wall applications

PRODUCT ATTRIBUTES

Product Type: PCB Retainer

Type: Shafted, High Clamp Force

Thermal Performance: Better

Profile: 0.250" x 0.270" / 6.35 x 6.26 mm

Clamp Force: 600 lbf / 272 kg

Gap Width: PCB + (0.28 - 0.31 in) / PCB + (7.0 - 7.9 mm)

ADDITIONAL PRODUCT DETAILS

Like all shafted Card Loks, the Series 260HC has a ridged shafted design for a more uniform clamping force over the length of the Card Lok, while maintaining wedge and body alignment for easier installation.

⚠️WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.