



**SCHROFF**

## 21070-124 DIGITAL CONTACT SENSOR (OUTPUT) FOR GUARDIAN MANAGEMENT GATEWAY



### KEY FEATURES

---

External sensor for the Guardian Management Gateway

A port is capable of monitoring up to 16 sensor devices with a total cable length of 40 meters

If an nVent SCHROFF Guardian sensor is connected, it appears in the web interface with type and serial number

Metal housing

Easy Mounting

2 x RJ 45 connection

Easy daisy chain with CAT6 patch cable (or higher shielding)

### PRODUCT ATTRIBUTES

---

Product Type: Sensor

Type: Digital Contact

Works With: Guardian Management Gateway

### ADDITIONAL PRODUCT DETAILS

---

External sensor monitoring digital inputs/outputs with 2 RJ45 connectors. Up to 16 sensors can be daisy chained over patch cables and connected to one Guardian Management Port.

### North America

All locations

+1.763.422.2661

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
[nVent.com](https://nVent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.