



SCHROFF

29714-016 LHX+ IN-RACK COOLER, AIR/LIQUID HEAT EXCHANGER, 10 KW, 230 V, 2 FANS, 6 U, 550D



KEY FEATURES

19" mountable Air/Liquid heat exchanger with fan

Easy replaceable fans without dismounting the heat exchanger

Coolant feed from top or bottom

PRODUCT ATTRIBUTES

Product Type: Air/Liquid Heat Exchanger

Works With: Varistar; Varistar CP

Width: 426 mm

Depth: 500 mm

Height: 266 mm

Supply Voltage: 230 V min

Redundant Power Supply: No

Coolant Feed: Bottom

ADDITIONAL PRODUCT DETAILS

RackChiller In-Row Coolers (IRC) are designed to deliver localized/supplemental energy efficient cooling in data centers. RackChiller IRC is a modular and scalable precision cooling solution that can replace or supplement traditional data center cooling infrastructure.

Please order separately: Monitoring via Control unit, water control package, display and door contact switch.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.