



31596-792 ADVANCEDTCA FRONT PANEL, REINFORCED, WITH SPRING LOADING FOR IEA LEVER HANDLE FOR DIE-CAST END PIECE, 8U, 6 HP, 1 MM, SST



KEY FEATURES

Configuration: Front panel with IEA handle (with/without spring loading)

PRODUCT ATTRIBUTES

Product Type: Front Panel

Accessory Type: Front panel

Material: Stainless Steel

Front Finish: Raw

Rear Finish: Raw

Rack Height: 8 U

Height: 323.15 mm

Rack Width: 6 HP

Width: 29 mm

Depth: 1 mm

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

AdvancedTCA front panel for spring-loaded IEA handle with die-cast end piece.

CERTIFICATIONS



North America

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.