

EA9500 RACKPOWER EHANDLE RFID AND KEYPAD



KEY FEATURES

Security Access Control Handle for nVent SCHROFF RackPower iPDU's

Single or dual authentication

Triple embedded proximity card reader supporting MIFARE Classic 4k - UID, MIFARE Plus 2k - UID, MIFARE DESFire 4k - UID, HIS iClass - UID, HID 125 kHz prox - CSN and EM125 kHz Prox - CSN

Remote lock/unlock and remote monitoring

Local lock status indicator with multi-color LED indicator

Dual sided visible LED alarm beacons to indicate power, environmental, or security alarm status for the rack

User customizable key lock for manual over-ride

Embedded humidity sensor and additional environmental sensor port

Local data storage of 200 user credentials and 500 local events

Customizable alarm, LED status, and access configuration settings

PRODUCT ATTRIBUTES

Product Type: Handle

Type: eHandle

Works With: RackPower

ADDITIONAL PRODUCT DETAILS

The security access control eHandle is an intelligent electromechanical locking system for server and networking cabinets. The eHandle seamlessly integrates with the network controller and RackPower iPDUs to serve as a hub for access control and environmental monitoring.

North America

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.