

CONNECT AND PROTECT

MiniPAC





Small Form Factor Cases – minipac

OVERVIEW				
MAIN KATALOG				
Cabinets 1				
Wall mounted cases 2				
Accessories for cabinets and wall mounted cases 3				

Subracks/ 19" chassis 6

Climate control . . 4

Electronics cases 5

Front panels, plug-in units 7 Systems 8

Power supply units 9

Backplanes 10

Connectors, front panel component system 11

Appendix 12



Small aluminium extrusion cases to hold PCBs

• For applications e.g. in industry, railway technology, test and measurement, communications and network technology

FIXING OPTIONS







VARIOUS DIMENSIONS/COLOURS



04812023





INDIVIDUAL SHAPES







5.138 | nVent.com/SCHROFF SCHROFF PRODUCT CATALOG '05/2018



Small Form Factor Cases - minipac

OVERVIEW

Overview 5.138

CONVENIENT SMALL CASE - FLEXIBLE ENOUGH FOR ALL YOUR REQUIREMENTS

- To accomodate standardised and non-standardised PCBs
- As desktop enclosure, for bolting (e.g. to a mounting plate) or for mounting on DIN support rail (DIN 43880)
- · High level of heat dissipation through large aluminimum surface of case
- · High stability
- Type of protection: IP 40



Trapezium shape

- Accommodates up to 3 PCBs of different heights -50, 60 or 65 mm and board depth 100 or 160 mm
- As desktop enclosure, for wall mounting or for mounting on DIN support rail (DIN 43880)



Rectangular shape

- Accommodates up to 4 standardised PCBs in euroboard format, height 100 mm (3 U) or up to 8 non-standardised PCBs, height 60 mm and board depth 160 mm
- · Versions as desktop enclosure or for wall mounting

Individual cases in aluminium extrusion - our minipac variety to your specifications

- · Other case lengths
- Other case shapes
- Cut-outs for lamps, switches, connectors, cable ducting, etc.
- · Individual printing of cover plates
- Surface finish anodised or powder-coated

30407004


Trapeziumshape . . 5.140


Rectagonal shape . . 5.141




Small Form Factor Cases - minipac

TRAPEZIUM SHAPE







Dimensions of body tube




Desktop version



Wall mounting (on long side of trapezoid)



Wall mounting (on short side of trapezoid)



For mounting on a DIN support rail (DIN 43880)

- Accommodates 3 non-standardised PCBs (height 50, 60 and 65 mm, depth 100/160 mm)
- PCB thickness 1.6 mm, spacing 15.24 mm (3 HP)
- · Different versions
 - · Wall mounting
 - For mounting on a DIN support rail (DIN 43880)
 - Desktop version

DELIVERY COMPRISES

Item	Qty	Description
1	1	Case, trapeziform, Al extrusion
2	2	Lateral cover plate, 2.5 mm, anodised
3	1	Fixing material kit, user manual

ORDER INFORMATION

Description	Length mm	Part no.
Case, trapeziform, Al extrusion, black anodised; lateral cover plates anodised, thickness 2.5 mm (no mounting option)	100.5	24814-008
Case, trapeziform, Al extrusion, black anodised, lateral cover plates anodised, thickness 2.5 mm (for wall mounting on long side of trapezoid)	100.5	24814-010
Case, trapeziform, Al extrusion, anodised; lateral cover plates anodised, thickness 2.5 mm (for wall mounting on short side of trapezium)	100.5	24814-011
Case, trapeziform, Al extrusion, black anodised; for DIN support rail mounting (DIN 43880); lateral cover plates anodised, thickness 2.5 mm (for mounting on a DIN support rail, DIN 43880)	160.5	24814-014
Accessories		
Rubber foot for desktop version, PU 4 pieces		21102-025

NOTE

04811053

- · On request:
- Other case lengths
- Cut-outs for LEDs, switches, connectors or couplings (USB, SUB-D)
- Individual printing on cover plate


5.140 | nVent.com/SCHROFF




Small Form Factor Cases - minipac


RECTANGULAR SHAPE






Dimensions of body tube





Desktop version

Wall mounting (on long side of rectangle)



Wall mounting (on short side of rectangle)

- Accommodates 4 standardised PCBs (height 100 mm, depth 160 mm) or rotated by 90° to accomodate 8 nonstandardised PCBs (height 60 mm, depth 160 mm)
- PCB thickness 1.6 mm, spacing 15.24 mm (2 HP)
- · Different versions
 - · Wall mounting
 - · Desktop version

DELIVERY COMPRISES

Item	Qty	Description
1	1	Case, rectangular, Al extrusion
2	2	Lateral cover plate, 2.5 mm, anodised
3	1	Fixing material kit, user manual

ORDER INFORMATION

Description	Length mm	Part no.
Case, rectangular, Al extrusion, black anodised; lateral cover plates anodised, thickness 2.5 mm (desktop version)	160.5	24814-024
Case, rectangular, Al extrusion, anodised; lateral cover plates anodised, thickness 2.5 mm (for wall mounting on long side)	160.5	24814-025
Case, rectangular, Al extrusion, anodised; lateral cover plates anodised, thickness 2.5 mm (for wall mounting on short side)	160.5	24814-027
Accessories		
Rubber foot for desktop version, PU 4 pieces		21102-025

NOTE

- On request:
- Other case lengths
- Cut-outs for LEDs, switches, connectors or couplings (USB, SUB-D)
- Individual printing on cover plate

North America

Warwick, RI, USA Tel +1.800.525.4682 San Diego, CA, USA Tel +1.800.854.7086

Europe, Middle East & India

Straubenhardt, Germany

Tel +49 7082 794 0

Betschdorf, France

Tel +33 3 88 90 64 90

Warsaw, Poland

Tel +48 22 209 98 35

Hemel Hempstead,

Great Britain

Tel +44 1442 24 04 71

Lainate, Italy

Tel +39 02 932 714 1

Dubai, United Arab Emirates

Tel +971 4 37 81 700

Bangalore, India

Tel +91 80 67152000

Istanbul, Turkey

Tel +90 216 250 7374

Asia Pacific

Shanghai, China

Tel +86 21 2412 6943

Singapore

Tel +65 6768 5800

Shin-Yokohama, Japan

Tel +81 45 476 0271

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER



nVent.com/SCHROFF