



SCHROFF

13100-147 PSU 19" AC/DC FOR COMPACTPCI SERIAL, 3 U, 8 HP, 312 W



KEY FEATURES

19" pluggable PSU for CompactPCI Serial applications

Active power factor correction and active current-share function

N+1 redundancy, hot swap

Output signaling: PS present, power failure, PS_ON and enable

I2C interface

High efficiency, > 90% at 220 VAC

PRODUCT ATTRIBUTES

Product Type: Power Supply

Type: 19" Switched-Mode

Works With: CompactPCI Systems

Input Voltage AC: 90 – 264 V

Power: 312 W

Number of Output Voltages: 2

Voltage 1: 12 V

Current 1: 25 A

Voltage 2: 5 V

Current 2: 2.5 A

Rack Height: 3 U

ADDITIONAL PRODUCT DETAILS

Pluggable 19" Power Supply, for CompactPCI applications. The Power Supply has a wide range AC input, a 12V DC Payload and +5 V DC Standby output.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.