

## 57272 INPUT CONNECTOR/CABLE ASSEMBLY FOR LED LIGHT 3M



### KEY FEATURES

Lights can be easily mounted vertically or horizontally.

Simple through-wiring based on a plug-and-play system.

### PRODUCT ATTRIBUTES

Product Type: Light

Type: Cabinet Light

Accessory Type: Lights

Length: 3000 mm

Color: Black

Finish: Smooth Matte

Input Voltage AC: 250 V max

Material: Plastic

Nominal Voltage: 250 V

Operating Temperature: 60 °C min

Width: 0.3 mm

### ADDITIONAL PRODUCT DETAILS

The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional

magnetic kits. A motion sensor is also available.

#### North America

All locations

+1.763.422.2661

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

#### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

#### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

#### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
[nVent.com](https://nVent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.