

iPDU Cross Reference Guide

CONNECT AND PROTECT



	RackPOWER	Geist/Vertiv	APC/Schneider	Raritan/Legrand	Eaton
Gigabit Ethernet	✓			✓	*Not standard
Redundant Network	✓	✓		✓	
Ethernet Cascading/Daisy Chain	64 max	50 max	4 max	16 max	8 max
DC Power Sharing	✓			✓	
USB Quick Configuration	✓	✓		✓	✓
Sensor Ports	2	1	1	1	1
Max Sensors	8	16	1	16	3
Electronic Lock Support	✓			✓	
Billing Grade Metering Accuracy	✓	✓		✓	✓
Metering Accuracy	+/- 1%	+/- 1%	+/- 3%	+/- 1%	+/- 1%
Font Size (Enlogic Current = 100%)	100%	100%	70%	55%	60%
Display Font Readability	Very High	High	Mid	Low	Low
Graphical Local Display	✓		✓	✓	✓
Local Language Support	8 Languages	8 Languages			7 Languages
Electronic Power Source Color Coding	✓				
Dual Display	✓				
Max Operating Temperature (N. Amer)	60°C	60°C	45°C	60°C	60°C
Max Operating Temperature (International)	60°C	60°C	60°C	60°C	60°C
Warranty Period	5 years	5 years	2 years	2 years	2 years

Vertiv and Geist are trademarks or registered trademarks of Vertiv Co

Schneider and APC are trademarks or registered trademarks of Schneider Electric SE and its subsidiaries

Raritan and Legrand are trademarks or registered trademarks of Legrand North America, its parent and/or subsidiaries

Eaton is a trademark or registered trademark of Eaton Corporation

Disclaimer: Data shown comes from company websites as of August 2019. Contact Enlogic to report/correct any errors.