

23021-604 TEST ADAPTOR FOR DIN CONNECTOR TYPE D, 3 U, 160 MM, U



KEY FEATURES

For DIN 41612 connectors, type D

2 different measuring fields: (1) current and voltage measurement (U/I): pluggable test bridges (2) voltage measurement (U): soldered test bridges

Header with pin diameter 0.6 mm for wire wrap (b)

Outer pin rows (pin 1a, c and pin 16a, c) with wider tracks for power supply (2 A per track)

PRODUCT ATTRIBUTES

Product Type: Test Adapter

Type: Type D

Connector Type: D32

Board Depth: 160 mm

Rack Height: 3 U

Measuring Field: Voltage

Number of Layers: 1

ADDITIONAL PRODUCT DETAILS

Test Adapter for Boards with DIN 41612 Connectors Type D to access test points on the board.

Test adaptor for DIN connector type D cannot be used in combination with the adapter of other types.



North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**