

## 57265 COMPACT LED-LIGHT 550LM MOTION SENSOR



### KEY FEATURES

---

Lights can be easily mounted vertically or horizontally.

Simple through-wiring based on a plug-and-play system.

### PRODUCT ATTRIBUTES

---

Product Type: Light

Type: Cabinet Light

Accessory Type: Lights

Length: 396 mm

Color: Black

Color Temperature: 5800 K

Depth: 40 mm

Finish: Smooth Matte

Input Voltage AC: 230 V max

Input Voltage DC: 24 V max

Material: Plastic

Nominal Voltage: 230 V

Operating Temperature: -20 to 55 °C

Weight: 0.24 kg

Width: 33 mm

## ADDITIONAL PRODUCT DETAILS

---

The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
[nVent.com](https://nVent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.