



SCHROFF

29714-022 LHX+ IN-RACK COOLER, AIR/LIQUID HEAT EXCHANGER, VARIABLE SPEED, 10 KW, 115 V, 2 FANS, 6 U, 550D



KEY FEATURES

19" mountable Air/liquid heat exchanger with fan

Easy replaceable fans without dismounting the heat exchanger

Coolant feed from top or bottom

UL Certified

PRODUCT ATTRIBUTES

Product Type: Air/Liquid Heat Exchanger

Width: 426 mm

Depth: 500 mm

Height: 266 mm

Supply Voltage: 115 V min

Redundant Power Supply: No

Coolant Feed: Bottom

Works With: Varistar; Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order separately: Monitoring via Control unit, water control package, display and door contact switch.

North America

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.