


30118-335 19" FRONT PANEL WITH D-SUB CUTOUT, 2X25-PIN, 3U, 4 HP, 2.5 MM, AL, RAL 7035



**KEY FEATURES**

19" Front Panel with Cutout for Sub-D, ST type 3 or FDDI

**PRODUCT ATTRIBUTES**

Product Type: Front Panel

Accessory Type: Front panel

Material: Aluminum

Front Finish: Painted

Rear Finish: Conductive

Color Code: RAL 7035

Rack Height: 3 U

Height: 128.4 mm

Rack Width: 4 HP

Width: 19.98 mm

Depth: 2.5 mm

Package Quantity: 1

## ADDITIONAL PRODUCT DETAILS

---

19" Front Panel with SUB-D Cut-Out or FDDI Cut-Out.

## CERTIFICATIONS

---



### North America

All locations  
+1.763.422.2661  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
[nVent.com](https://nVent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.