



**SCHROFF**

## 21630-379 VARISTAR CP SHORTENED REAR PANEL AT BOTTOM, EMC, GLAZED STEEL, 1800H 800W



### KEY FEATURES

---

Screw fixed, Robust and Single person mountable Side Panel

Height of connection plate 400 mm

The height of the rear panel is 400 mm less than the cabinet height

Interior galvanized

### PRODUCT ATTRIBUTES

---

Product Type: Cabinet/Rack Panel

Product Family: Varistar CP

Material: Stainless Steel

Rack Height: 38 U

Height: 1800 mm

Width: 800 mm

Protection Rating: IP55

### ADDITIONAL PRODUCT DETAILS

---

Shortened rear panel with mounting plate now available as a complete SKU for better cable management.

Please purchase the grounding kit separately.

### North America

All locations

+1.763.422.2661

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
[nVent.com](https://nVent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.