

60118-563 ADJUSTABLE MONITOR ARM WITH KEYBOARD TRAY (VAMONITOR)



**KEY FEATURES**

Support arm for mounting of flat screen monitor, keyboard and mouse on

Fixing is to the side of the Heavy-Duty frame

Static load-carrying capacity of arm maximal 8 kg, static load-carrying capacity of keyboard maximal 2.5 kg

Support arm: Height-adjustable 300 mm; Angle of rotation on cabinet 180 °; Monitor rotation angle 340° (fitted on cabinet 270°); Monitor tilt angle 60°; Integrated cable routing

Suitable for industrial and laboratory applications

Keyboard and Mouse storage place

**PRODUCT ATTRIBUTES**

Product Type: Monitor Arm

Works With: Cabinet

## ADDITIONAL PRODUCT DETAILS

---

Pendant arm with keyboard tray with high flexibility and operability to connect HMI for the operator The collapsible articulate arm is ideal for a rack mounted stand workstation. It's an easy to install rack mountable appendage which allow panoramic movement possibilities for mounting a flat screen monitor and keyboard & mouse in industrial environments.

### North America

All locations

+1.763.422.2661

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
[nVent.com](https://nvent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.