

21630-554 VARISTAR CP REAR PANEL, SCREW FIXED, GLAZED STEEL, 42 U, 2000H 800W, IP55, EMC



KEY FEATURES

Screw fixed, Robust and Single person mountable Side Panel

Rear panel without grounding kit

PRODUCT ATTRIBUTES

Product Type: Cabinet/Rack Panel

Product Family: Varistar CP

Type: Rear Panel

Works With: Varistar CP

Material: Steel

Finish: Powder Coated

Rack Height: 42 U

Height: 2000 mm

Width: 800 mm

Protection Rating: IP55

ADDITIONAL PRODUCT DETAILS

Cabinets have rear panels well screwed to the frame to have maximum contact with the gasket.

Please purchase the grounding kit separately.

North America

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.