

Varistar Colocation Cabinets



SCHROFF

MAXIMUM ACCESS PROTECTION AND FLEXIBLE CABLE MANAGEMENT



With the new SCHROFF branded Varistar colocation cabinet series, nVent offers a secure cabinet with multiple compartments that has been specially developed for IT infrastructure and data centers.

The Varistar colocation cabinet is available with two, three or four compartments in eight different cabinet dimensions. Additional cladding and extension components from our standard product portfolio can be configured at any time.

It features secure shelf dividers and cable routings that are attached to the frame at multiple points.

The shelf dividers and cable routings of each compartment are strictly separated from one another. This provides the highest level of security for the access to the components installed in the compartments. Owing to their design, it is also possible to use the shelf dividers as cable trays.

Two-point door locking provides additional security plus robustness and is equipped with combination locks (numeric code and master key) as standard.

The well-designed cable management ensures separation of data and power cables and allows cable entry from above and below and from left and right.

ADVANTAGES AND BENEFITS OF VARISTAR COLOCATION CABINETS

- Wide selection of standard dimensions and configurations
- Short delivery time of 10 working days
- Sophisticated infrastructure solutions and product combinations
- Secure locking
- Flexible cable ducting with separation of data and power cables

Varistar Colocation Cabinets



Side view

- Cable entry from left and right into each compartment
- Lateral cable routing for each compartment through entire cabinet height



Interior view of compartment

- Shelf divider also acts as cable tray



Interior view with open door

- 2-point locking for optimal security

Compartments	Height (mm)	Width (mm)	Depth (mm)	Part number
2	2000	600	1000	10130-202
		800		10130-205
		600	1200	10130-214
		800		10130-217
3	2000	600	1000	10130-203
		800		10130-206
		600	1200	10130-215
		800		10130-218
4	2000	600	1000	10130-204
		800		10130-207
		600	1200	10130-216
		800		10130-219
2	2200	600	1000	10130-208
		800		10130-211
		600	1200	10130-220
		800		10130-223
3	2200	600	1000	10130-209
		800		10130-212
		600	1200	10130-221
		800		10130-224
4	2200	600	1000	10130-210
		800		10130-213
		600	1200	10130-222
		800		10130-225

For further information please visit: nVent.com/SCHROFF

Europe

Straubenhardt, Germany
Tel: +49.7082.794.0
Betschdorf, France
Tel: +33.3.88.90.64.90
Warsaw, Poland
Tel: +48.22.209.98.35
Hemel Hempstead,
Great Britain
Tel: +44.1442.24.04.71
Lainate, Italy
Tel: +39.02.932.714.1

North America

Warwick, RI, USA
Tel: +1.800.525.4682
San Diego, CA, USA
Tel: +1.800.525.4682

Middle East & India

Dubai, United Arabian
Emirates
Tel: +971.4.37.81.700
Bangalore, India
Tel: +91.80.6715.2001
Istanbul, Turkey
Tel: +90.216.250.7374

Asia

Shanghai, P.R. China
Tel: +86.21.2412.6943
Singapore
Tel: +65.6768.5800
Shin-Yokohama, Japan
Tel: +81.45.476.0271



nVent.com

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER