



Item Number
60110-470

Single phase monitored PDU

Input Rating : 16A, 230V
Outlet : 10A Rated C13 x 40
Inlet : 16A IEC60309 2P+E plug x 2
Cordset : 3 meter 1.5mm sq. H05V V-F cordset x 2
Protection : 16A resettable fuse x 2
Circuit Details : < PDU I > Output 16A max. C 13 #1 - 20
< PDU II > Output 16A max. C 13 #1 - 20

Meter Features (W monitored PDU)

Local Display : Field replaceable 2.8" color LCD with touchscreen
Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
Accuracy : ±1% Billing-grade
IP Access : via IP dongle, one IP Access up to 16 PDU Levels
Cascade : Up to 16 PDU under single IP address via IP dongle
SNMP : V2 / V3 via IP dongle
Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance	:	CE / EMC certified
Safety Compliance	:	CE / LVD certified
Environment Compliance	:	RoHS2 & REACH
Operating Temperature	:	-5 to 60 °C
Storage Temperature	:	-25 to 65 °C
Operating Altitude	:	0 to 2,000 m
Storage Altitude	:	0 to 15,000 m
Humidity	:	8 to 95% RH, non-condensing
Dimension	:	85 (W) x 90 (D) x 1650 (H) mm
Material	:	Steel
Color	:	PDU I - red / PDU II - blue (outlet bracket) Black (chassis)