

Basic PDU Data Sheet – EN2.0 Series

The EB0305 Basic PDU offers a cost-effective option to users who do not require intelligence. Premium hydraulic-magnetic circuit breakers operate reliably in high temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, Enlogic's standard low-profile design, and toolless mounting backed by a 5-year hassle free warranty.

Electrical Input

Input Plug Type	IEC 60309 363P6
Acceptable input voltage	200-240VAC, 1ph
Input current (<i>phase</i>)	63A
Input frequency	50/60 Hz
Max Input power	15.1 kVA @ 240 VAC

Electrical Output

Output voltage	230 V
Maximum output current (<i>phase</i>)	63A
Overload protection (<i>internal</i>)	(6) 1-pole, 16A hydraulic-magnetic circuit breakers
Outlet configuration	(6)C19

Physical

Chassis Dimensions (L x W x D) in	1.71 x 17.46 x 7.77
Depth at circuit breaker, in	NA
Input cord length	12'

Environmental

Operating Temperature	-5 to 60°C (23 to 140°F)
Storage Temperature	-20 to 60°C (-4 to 140°F)
Humidity (operating/storage)	5-90% RH / 5-95% RH; non-condensing
Max operating elevation, above MSL	3,000 m (9,840 ft)

Compliance

Safety & Environmental	CE, Demko Certified to IEC/EN60950-1, RoHS, REACH
------------------------	---

Warranty and Terms

Warranty

CIS Global warranties Enlogic brand equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser. For full warranty details, please visit www.enlogic.com/warranty.



Disclaimer

Copyright © 2019, CIS Global LLC and/or its affiliates. All rights reserved. This document is provided for information purposes only and current at the time of publishing; the contents hereof are subject to change without notice. This document is not warranted to be error-free, nor subject to any other warranties or conditions, whether expressed orally or implied in law, including implied warranties and conditions of merchantability or fitness for a particular purpose. We specifically disclaim any liability with respect to this document, and no contractual obligations are formed either directly or indirectly by this document. This document may not be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, without our prior written permission. Enlogic is registered trademark of CIS Global LLC and/or its affiliates.

About CIS

CIS Global has delivered superior product development, manufacturing, and logistics management since 1955 to small and large customers across the globe. We specialize in data center products including mechanical motion and power management solutions. As world market share leader in precision server rails and OEM market share leader in PDUs, CIS designed and built products are found in nearly every data center worldwide.

CIS has more than 20 years' experience manufacturing more than 2-million best-in-class PDUs. CIS acquired Enlogic in 2015 and remains dedicated to providing the industry's most innovative power management solutions build with the highest manufacturing quality.

Americas	Europe/Middle East	Australia & New Zealand	Asia		
USA	UK	Australia	Hong Kong	India	Taiwan
+1 (636) 821 5200	+44 (1905) 401700	+61 (39) 9997303	+852 (58) 016700	+91 (800) 4430029	+886 (801) 491390
AMERsales@cisww.com	EMEAsales@cisww.com	ANZsales@cisww.com	APACsales@cisww.com		