


Adresse/Address: Schroff S.A.S. F-67660 Betschdorf
 Ce plan et les informations contenues sont la propriété de SCHROFF S.A.S. REPRODUCTION ET DIFFUSION INTERDITES SAUF AUTORISATION PREALABLE.
 This document and the informations it contains are property of SCHROFF S.A.S. REPRODUCTION AND DISCLOSING ARE PROHIBITED WITHOUT PRIOR WRITTEN CONSENT.

SL frame represented.
Valid for SL and HD frame.

900	1200	750	1125.5
900	1100	750	1025.5
900	1000	750	925.5
900	900	750	825.5
900	800	750	725.5
900	700	750	625.5
900	600	750	525.5
900	500	750	425.5
900	400	750	325.5
900	300	750	225.5
800	1200	650	1125.5
800	1100	650	1025.5
800	1000	650	925.5
800	900	650	825.5
800	800	650	725.5
800	700	650	625.5
800	600	650	525.5
800	500	650	425.5
800	400	650	325.5
800	300	650	225.5
600	1200	450	1125.5
600	1100	450	1025.5
600	1000	450	925.5
600	900	450	825.5
600	800	450	725.5
600	700	450	625.5
600	600	450	525.5
600	500	450	425.5
600	400	450	325.5
600	300	450	225.5
Width	Depth	L	P



Projectname:/Use:/Utilisation: VAR I STAR				Oberfl./Surface:/T.de Surface:		Freimaß-Tol. ISO 2768-mK	
Maßstab/Scale/Echelle: **				Werkstoff:/Material:/Matiere: ***		Nennmaßbereich Corresp. Tol. Dim. nominale	
a	08/2543	11/02/08	URBES	Benennung:/Title:/Designation: Position standard des pieds		Abmaße Dim. limits Tolerances	
Ind SYM	Ändr./Revision Modification	Datum Date	Name Nom	Z.Nr./Drawing No./Nr. du document.		intern	Rev./Mod. Bl/Pg
Freig./Rel./Relach.	**.*.*.*		***	70139-16400000		1/1	Status 012
Norm/Revision	11.02.08		HAVEN	Gez./Drawn/Des.		08.02.08	URBESF
Ersatz für: replace/remplace:			MD	.. - *			