



SCHROFF

11990-600 ATCA SYSTEM 300/40 SERIES, 14 SLOT, DC, DUAL STAR, BUSSED IPMB



KEY FEATURES

Conforms to AdvancedTCA Standard PICMG 3.0 rev. 3.0

Input voltage -48 VDC/ -60 VDC, two redundant power entry modules (PEM)

Redundant hot-swap fan trays, airflow from bottom front to top rear; air filter access from front

300 W cooling capacity per slot at an ambient temperature of 55 °C

Prepared for two SCHROFF shelf managers with Pigeon Point ShMM 700

Shelf alarm panel (SAP) and shelf alarm display (SAD)

UL recognized, E229721 type T07

PRODUCT ATTRIBUTES

Product Type: System

Number of Slots: 14

Type: 19" Rack Mount

Backplane Type: Dual Star, Bussed IPMB

Data Transfer: 40 GbE

Power per Slot: 300 W

Input Voltage DC: -48 V; -60 V

Airflow Direction: Front to Rear

Rack Height: 13 U

Power Supply Type: (2) DC PEM

Power Supply Included: Yes

Rear I/O: Yes

Complies With: PICMG 3.0 R3.0

Depth: 383 mm

ADDITIONAL PRODUCT DETAILS

The nVent SCHROFF ATCA 300/40 Series is a family of AdvancedTCA Shelves that provide cooling and power per slot for 300 W blades. The backplane is verified in accordance to 40GBASE-KR4 for 40 Gbit Ethernet.

Modified systems available on request.

Completely assembled, cabled and tested.

CERTIFICATIONS

The logo features the word "ROHS" in a large, bold, black font with a green checkmark above the letter "O". Below it, the word "COMPLIANT" is written in a smaller, green, sans-serif font.



North America

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.