

10630-031 VARISTAR CP ON-BOARD CABINET, ROLLING STOCK, RAILWAYS, 38 U 1800H 600W 400D



### KEY FEATURES

---

EN 50155 Shock n Vib certified

Static load-carrying capacity 1600 kg

Type of Protection IP55

Railway certified welding per EN 15085-2

### PRODUCT ATTRIBUTES

---

Product Type: Cabinet

Product Family: Varistar CP

Frame Material: Steel

Rack Height: 38 U

Height: 1800 mm

Width: 600 mm

Depth: 400 mm

Static Load: 1600 kg

Protection Rating: IP55

Complies With: EN 50155; IEC 60529; IEC 61587-1; IEC 60297-3-100; IEC 61587-2; EN 45545-2

Color: Black Grey

Color Code: RAL 7021

Frequency: 150 Hz

Material: Steel

Works With: Varistar CP

## ADDITIONAL PRODUCT DETAILS

For operation in mobile environments, electronic systems require a physical construction capable of withstanding extreme conditions in harsh environments.

nVent SCHROFF cabinets are therefore designed to protect the electronics they house with high levels of mechanical stability and resistance to shock and vibration, according to EN 50155, EN 45545, CENELEC and AREMA.

### North America

All locations

+1.763.422.2661

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)

### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[schroff.nvent.com](https://schroff.nvent.com)



Our powerful portfolio of brands:  
[nVent.com](https://nvent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.