



SCHROFF

15B-7-3 15 PCB-TAINER



KEY FEATURES

Available unplated or with silver, copper, gold, nickel, zinc clear chromate, or zinc yellow chromate plating

Constructed from beryllium copper or stainless steel

Weight 0.63 g/cm (0.056 oz/")

For sheet metal applications

Mounts to the enclosure with standard rivets, eyelets or screws

Height 4.35 mm (0.171")

Width 12.7 mm (0.50")

Length 50.8 mm (2.0") to 254.0 mm (10.0"), 12.7 mm (0.5") increments

Spring based retention design

Supports PCB thickness of 1.59 mm (0.063")

Mounting hole $\varnothing 2.77 +0.03\ -0.08$ ($\varnothing 0.109 + 0.001\ - 0.003$)

PRODUCT ATTRIBUTES

Product Type: PCB Retainer

Type: PCB Tainer (Spring Design)

ADDITIONAL PRODUCT DETAILS

The Series 15 PCB Tainer is ideal for PCB retention within low shock and vibration applications.

⚠WARNING: This product can expose you to chemicals including beryllium, which is known to the State of California to cause cancer. For more information, go to www.P65Warnings.ca.gov.

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those

referenced by the customer.

CERTIFICATIONS



North America

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.