



SCHROFF

MA280HTS-4.30TM3L 280HTS HIGH THERMAL SAWTOOTH CARD-LOK



KEY FEATURES

New sawtooth profile design for advanced thermal performance

Profile 9.72mm (0.365") x 9.65 mm (0.375")

Weight 2.50 g/cm (0.022 oz/")

Length 71.12 mm (2.8") to 325.12 mm (12.80"), 12.7 mm (0.5") increments

Flexible mounting options

Average clamp force at 113 N-cm (10"-lbs) torque 554 kg (1219 lbs)

Screw actuated

Max expansion 11.68 mm (0.460")

Available with black anodized or electroless nickel plating

For cold wall applications

PRODUCT ATTRIBUTES

Product Type: PCB Retainer

Type: High Thermal Sawtooth

Thermal Performance: Best

Profile: 0.365" x 0.375" / 9.27 x 9.65 mm

Clamp Force: 600 lbf / 272 kg

Gap Width: PCB + (0.39 - 0.43 in) / PCB + (10.0 - 10.9 mm)

ADDITIONAL PRODUCT DETAILS

The 280HTS features a unique sawtooth profile design that provides advanced thermal performance and clamping force compared to similarly sized card locks for superior thermal dissipation and protection in high shock and vibration applications. The 280HTS can be a drop in replacement for most existing Series 280 card lok applications.

⚠WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

From time to time, nVent may modify its product specification to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

Applications: The Series 280HTS features sawtooth designed profiles along the length of the Card Lok that provide a continuous and uniform surface along the PCB/heat frame and along the cold wall for superior cooling performance.

Average Junction Resistance: Depends on lengths and application.

Average Clamping Force: 554 kg (1219 lbs.) at 113 N-cm (10"-lbs).

Order Information: For customized products contact AskSchroff@nVent.com or 1-800-854-7086. Please provide drawing, quality clauses, and purchase order requirements.

Recomendet Gap width: PCB + 10.29 mm (0.405 in).

CERTIFICATIONS



North America

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.