



SCHROFF

MHA224-7.30ETM2 224 TORQUE LIMITING CARD-LOK



KEY FEATURES

Clamp force, thermal transfer, life cycle and environmental (MIL 810) test results available

Available with gold chem film, clear chem film, black anodized, hard black anodized, or electroless nickel plating

Profile 5.33 mm (0.210") x 7.24 mm (0.285")

5 segment, non-shafted design

Each unit tested at factory prior to shipment to ensure performance; customer provided with a certificate of conformance

For cold wall applications

Length 97 mm (3.80") to 325 mm (12.80"), 12.7 mm (0.5") increments

Min expansion 8.64 mm (0.340")

Flexible mounting options

Weight 1.12 g/cm (0.100 oz/')

Average clamp force (4.80", black anodized) = 236 lbs

Torque limiting; ideal for 2nd level maintenance

Screw actuated

PRODUCT ATTRIBUTES

Product Type: PCB Retainer

Type: Non-shafted

Thermal Performance: Good

Profile: 0.210" x 0.285" / 5.33 x 7.24 mm

Clamp Force: 200 – 299 lbf / 91 – 136 kg

Gap Width: PCB + (0.32 - 0.35 in) / PCB + (8.0 - 8.9 mm)

Design Feature: Torque Limiting

ADDITIONAL PRODUCT DETAILS

The Series 224 Card-Lok is ideal for field level maintenance, because it does not require any specialized tools or technical knowledge for proper installation. With an integrated (patented) torquing mechanism, to install the Series 224, the operator simply turns the hex wrench until they hear/feel a minimum of three clicks indicating that the optimum clamping and thermal transfer performance has been reached. Accordingly, the Series 224 Card Lok minimizes the potential for insufficient board retention from under torquing, or for damage to board and cold wall from over torquing.

⚠️WARNING: This product can expose you to chemicals including Chromium (hexavalent compounds), which is known to the State of California to cause cancer and reproductive health issue. For more information, go to www.P65Warnings.ca.gov.

From time to time, nVent may modify its product specifications to be in conformity with applicable industry, military or other relevant standards. Unless otherwise mutually agreed in writing, cancelled or superseded military specifications may be certified to the latest or superseding specifications. Products manufactured in conformity with such specifications will be deemed fully compliant whether or not you have been notified of such modifications, even if different from the original specification or those referenced by the customer.

CERTIFICATIONS



North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2024 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.