


Date : 11 Nov 19
Version : V1


3-Phase 400V 32A switched PDU drawing & specification

RP2000: Strip level measurement, Outlet Switch ON / OFF, SNMP Hardware

RackPower



Item Number
60110-466



Three phase switched PDU

Input Rating : 32A, 400V 3PH
Outlet : 10A Rated C13 x 21
16A Rated C19 x 3
Inlet : 32A IEC60309 3P+N+E 6hr Red plug
Cordset : 5-wire 3 meter 4.0mm sq H07RN-F cordset
Protection : 16A resettable fuse x 6
Bank Details : **PH-1 < Bank 1 >** Output 16A max. C13 #1-4
< Bank 2 > Output 16A max. C13 #5-7 + C19 #C1
PH-2 < Bank 3 > Output 16A max. C13 #1-4
< Bank 4 > Output 16A max. C13 #5-7 + C19 #C1
PH-3 < Bank 5 > Output 16A max. C13 #1-4
< Bank 6 > Output 16A max. C13 #5-7 + C19 #C1

Meter Features (WS Switched PDU)

Local Display : Field replaceable 2.8" color LCD with touchscreen
Bank Measurement : Voltage (V), Current (A), energy (kWh) & power factor
Outlet Control : Outlet Switch ON / OFF
Accuracy : $\pm 1\%$ Billing-grade
IP Access : via IP dongle, one IP Access up to 16 PDU Levels
Cascade : Up to 16 PDU under single IP address via IP dongle
SNMP : V2 / V3 via IP dongle
Sensor Port x 2 : Temp. Sensor / Temp. + Humid. Sensor

EMC Compliance : CE / EMC certified
Safety Compliance : CE / LVD certified
Environment Compliance : RoHS2 & REACH

Operating Temperature : -5 to 60 °C
Storage Temperature : -25 to 65 °C
Operating Altitude : 0 to 2,000 m
Storage Altitude : 0 to 15,000 m
Humidity : 8 to 95% RH, non-condensing

Chassis Material : Steel
Chassis Color : Black

Product Dimension : 54 (W) x 80 (D) x 1700 (H) mm
Net Weight : 8 kg

Packing Dimension (for 2 PDUs) : 110 (W) x 268 (D) x 2043 (H) mm
PDU Gross Weight (for 2 PDUs) : 18 kg