

Series 236 Card-Lok

CONNECT AND PROTECT



RECOMMENDED GAP WIDTH

PCB + 8.00 (.315)

RECOMMENDED TORQUE

68 N-cm (6 in-lbs)

WEIGHT

1.34 g/cm (.120 oz/in)

MATERIALS AND FINISH


WEDGES

- **Material:** Aluminum Alloy 6061-T6 per ASTM-B221 or AMS-QQ-A-200/8
- **Finish:** See finish table on opposite page


SCREW

.09-in. or 2.5-mm hex. socket head cap screw, depending on mounting configuration

- **Material:** Stainless steel per ASTM A-582
- **Finish:** Passivated per AMS2700



SERIES 236 CARD-LOK



Part Number Code

Series 236 Card-Lok Five Piece

S A 236 5.80 E TM2.5 P

Prefix options

Slotted Drive _____ S

2mm Hex Drive _____ [blank]

Finish options

Black Anodize _____ A

or choose from Finish Table

Assembly length in inches. Standard lengths range from 121.9 (4.80) to 325.12 (12.8) in 12.7 (0.5) increments ____ length.xx
 Other lengths available upon request

Additional Center Mounting Hole _____ E

None _____ [blank]

Mounting Options - M2.5 tapped hole _____ TM2.5

or choose from Mounting Option Table _____ see table

Locking Insert Option _____ P

None _____ [blank]

FINISH TABLE

Code Letter	Finish
[blank]	Chemical Film per Mil-DTL-5541 Class 1A, Type 1, Gold
"R"	Chemical Film per Mil-DTL-5541 Class 3, Type II, Clear
"A"	Black Anodize per Mil-A-8625 Type II, Class 2
"HA"	Hard Black Anodize per Mil-A-8625 Type III, Class 2
"EN"	Electroless Nickel per Mil-C-26074 Class 4, Grade B, Bright

MOUNTING METHOD TABLE

Code Letter	Method
[blank]	No mounting holes
"T0"	0-80 tapped hole
"T2"	2-56 tapped hole
"TM2"	M2 x 0.40 tapped hole
"TM2.5"	M2.5 x 0.45 tapped hole

Part Number Code Example:

A236-2.80ETM2.5

Series 236 Card-Lok five piece, black anodized, 71.12 (2.80) assembly length, with three M2.5 tapped mounting holes.

nVent SCHROFF, Inc.

7328 Trade Street
 San Diego, CA 92121 USA
 +1 800-525-4682

CALMARK™



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER