


# Series 125, 126 Retainers

CONNECT AND PROTECT



## WEIGHT

.40 g/cm (.036 oz/in)

## MATERIALS AND FINISH


- **Material:**  
.41 (.016) thick Stainless Steel Type 301, Cond.  
1/2 H, ASTM -A240
- **Finish:**  
Sassivated per MILS-5002

## SPRING RATE

60.4N/cm (34.5lbs/in)  
of deflection per spring finger

Dash No.	PCB Thickness	B Dimension +0.38 (.015) -0.0 (.000)	G Dimension +0.0 (.00) -0.80 (.03)
-06	1.6 (1/16)	1.91 (.075)	1.14 (.045)
-09	2.4 (3/32)	2.67 (.105)	1.91 (.075)

125 Shown, 126 Opposite



Part Number Code			
PCB Thickness		125 or 126	-06 - 3.25
1.6 (.063)		06	
2.4 (.094)		09	
Length			3.25
31.75 (1.25) to 311.15 (12.25)			
in 25.4 (1.00) increments			
Other lengths available on request			

Part Number Code Example:

125-06-4.25  
Series 125 passivated stainless steel,  
107.95 (4.25) long designed for 1.6 (.063)  
thick printed circuit boards

nVent SCHROFF, Inc.

7328 Trade Street  
San Diego, CA 92121 USA  
+1 800-525-4682

CALMARK™



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER